

Socket Clevis

By ANDERSON
Catalog # [876032000](#)

Socket clevises are used primarily for connecting associated hardware to ball and socket type insulators.



*Representative Image

Features

- Ultimate strength is 30,000 lbs. (133 kN)
- Length - 2.625"
- Clevis Eye Opening Width - 0.813"
- Clevis Pin Hole Diameter - 0.625"
- Material: Body - galvanized ductile iron, Clevis Pin - galvanized steel, Cotter Pin - stainless steel
- For use with ANSI class 52-3 & 52-5 insulators per ANSI Spec. C29.2-71.

General

Catalog Number	876032000
Material	Ductile Iron
Material - Pin (Clevis)	Galvanized Steel
Material - Pin (Cotter)	Stainless Steel
Number of Bolt Holes	0
Series	SC Series
Strength Rating - Ultimate	30000 lb
Strength Rating - Ultimate	0 lb
Body	
UPC	096359252542

Dimensions

Assembly Rating (Ultimate)	0 lb
Clevis Opening	0.813 in
Diameter - Bolt	0 in
Diameter - Pin	0 in
Dimensions	2.313 in x 4.13 in x 2.63 in

Height	2.63 in
Insulator Throat Diameter - Maximum	0 in
Insulator Throat Diameter - Minimum	0 in
Insulator Throat Diameter Range	0 - 0
Length	2.313 in
Length - Coupling	2.625 in
Length - Pin	0 in
Maximum Adjustment	0 in
Ring Height	0 in
Weight	2.646 lb
Width	4.13 in

Conductor Related

Conductor Diameter - Maximum	0 in
Conductor Spacing	0 in

Certifications And Compliance

Buy America(n) Qualified	TAA Compliant (All status valid till December 2024)
--------------------------	---

Product Assets

[Catalogs - Transmission Connectors Catalog - Full](#)
[Sales Drawings - 876032000 CUTSHEET](#)
[Specifications - 876032000](#)