



\* Representative image

# Stud Connector, Aluminum

by ANDERSON  
Catalog ID: ADSC1479012

Stud Connector, Aluminum, 1-1/2-12 Stud to Cable 0.563-0.744, 90 degree.  
STUD, AL 1-1/2-12, .563-.744 IN, 90 DEG

## Product Details

### General

Material	Aluminum
Material - Clamping Hardware	Aluminum Alloy
Number of Ground Braid Lug Holes	0
Number of Stud Threads	12
Type	Stud to Cable
UPC	096359281818

### Dimensions

Angle - Stud to Conductor	90 °
Base Hole Spacing	0 in
Diameter - Base Holes	0 in
Diameter - Bolt	0 in
Diameter - Inside	0 in
Diameter - Stud	1.5 in
Length - Coupling	0 in
Length Before Compression	0 in
Weight	1.274 lb

### Electrical Ratings

Maximum Current Rating Amps Continuous	0
--	---

### Conductor Related

Conductor Compatibility	ACSR-Penguin-4/0-6/1;ACSR-Waxwing-266.8-18/1;ACSR-Partridge-266.8-26/7;ACSR-Ostrich-300-26/7;ACSR-Merlin-336.4-18/1;ACSR-Linnet-336.4-26/7;ACSR-Oriole-336.4-30/7;ACSR-Chickadee-397.5-18/1;ACSR-Brahma-203.2-16/19;AAC-Valerian-250-19;AAC-Laurel-266.8-19;AAC-Tulip-336.1-19;AAC-Daffodil-350-19;AAC-Canna-397.5-19
Conductor Diameter - Maximum	0.744 in
Conductor Diameter - Minimum	0.563 in
Conductor Diameter Range	0.563 - 0.744
Conductor Type	<ul style="list-style-type: none"> <li>• AAC</li> <li>• ACSR</li> </ul>

**For further technical assistance, please contact us**

**Domestic Customer Service**

Hubbell Power Systems  
210 N. Allen Centralia, MO 65240 USA  
Phone: (573) 682-5521  
Fax: (573) 682-8475  
Email: [hpscsc@hubbell.com](mailto:hpscsc@hubbell.com)

**International Customer Service**

Phone: +1-573-682-5521  
Fax: +1-573-682-8516  
Email: [hpsintlcs@hubbell.com](mailto:hpsintlcs@hubbell.com)