

HUBBELL Power Systems

Ball Eye - 50k lb

By ANDERSON

Catalog # [909462000](#)

Ball eyes are used to attach ball and socket insulators to other associated hardware. The use of the ball oval-eye and an anchor shackle is one of the most common distribution tower attachment combinations.



*Representative Image

Features

- Ultimate strength is 50,000 lbs. (222kN)
- Eye: 1.250 x2.500" Opening x 0.750" Thick
- Material: Body - Galvanized Forged Steel
- For use with class 52-8 and 52-11 insulators per ANSI Spec. C-29.2.71.

General

EU RoHS Indicator	No
Material	Steel
Number of Bolt Holes	0
Series	BE Series
Strength Rating - Ultimate	50000 lb
Strength Rating - Ultimate Body	0 lb
UPC	096359252801

Dimensions

Assembly Rating (Ultimate)	0 lb
Diameter - Bolt	0 in
Diameter - Pin	0 in
Insulator Throat Diameter - Maximum	0 in
Insulator Throat Diameter - Minimum	0 in
Insulator Throat Diameter Range	0 - 0
Length - Coupling	4.5 in
Length - Pin	0 in
Maximum Adjustment	0 in
Ring Height	0 in
Weight	1.548 lb

Conductor Related

Conductor Diameter - Maximum	0 in
Conductor Spacing	0 in

Logistics

Pallet Quantity 1344

Product Assets

[Catalogs - Transmission Connectors Catalog - Full](#)

