



* Representative image

ALRC045LWE

by Acme Electric

Catalog ID: ALRC045LWE

Prop65_Cancer&Reproductive

AC Line Reactor - Three Phase, 240 Volts 10% Z - 480 Volts 5% Z - 600 Volts 4% Z, 817 uH, 45 A, CE Marked, Encapsulated

- Protects from damaging voltage drop
- Eliminates nuisance tripping
- Reduces surges and spike currents
- Longer life for motors and solid state components

Product Details

General

| | |
|----------------------|---------------------|
| CE Compliant | CE Marked |
| Construction | Encapsulated |
| Inductance | 817 uH |
| Inductance Range | 751+ uH |
| Max Temperature Rise | 115 Degrees Celsius |
| Motor Power | 30 HP |
| Mounting Type | Wall |
| Primary Voltage | 240V / 480V / 600V |
| Product Category | AC Line Reactor |
| Reactor Current | 45 A |
| UL Insulation Class | 180°C |
| UPC | 047503096642 |
| Winding Material | CU |

Dimensions

| | |
|--------|----------|
| Height | 11.83 in |
| Length | 11.83 in |
| Weight | 75 lb |
| Width | 11.83 in |

Electrical Ratings

| | |
|------------------|---------------|
| Frequency Rating | 60 Hz |
| Primary Voltage | 240/480/600 V |

Certifications and Compliance

| | |
|--------------|-----------|
| CE Compliant | CE Marked |
|--------------|-----------|

| | |
|--------------|-------------|
| CSA Standard | C22.2 No 66 |
| Nema Rating | NEMA 3R |
| UL Standard | UL 506 |