

HUBBELL

Power Systems

Anchor Shackle - 100k lb

By ANDERSON
Catalog # [946693001](#)

Anchor Shackles are used to attach hardware to the tower pad. Back to back anchor shackles are commonly used at the tower attachment point to orient the plane of the tower plate and the balance of the insulator hardware.



Features

- Ultimate strength is 100,000 lbs. (445 kN)
- Opening Width: 1.188 inches
- Bolt Diameter: 1.125 inches
- This shackle is type BNK which is furnished with Bolt, Nut and Cotter Key
- Material: Body - galvanized steel, Hardware - galvanized steel, Cotter Pin - stainless steel

General

EU RoHS Indicator	No
Material	Steel
Material - Pin (Clevis)	Galvanized Steel
Material - Pin (Cotter)	Stainless Steel
Number of Bolt Holes	0
Series	AS Series
Strength Rating - Ultimate	100000 lb
Strength Rating - Ultimate Body	0 lb
UPC	096359253211

Dimensions

Assembly Rating (Ultimate)	0 lb
Clevis Opening	1.188 in
Diameter - Bolt	0 in
Diameter - Pin	0 in
Height	2.38 in
Insulator Throat Diameter - Maximum	0 in
Insulator Throat Diameter - Minimum	0 in
Insulator Throat Diameter Range	0 - 0
Length	5.31 in
Length - Coupling	4.313 in
Length - Pin	0 in
Maximum Adjustment	0 in
Ring Height	0 in
Weight	6.77 lb

Conductor Related

Conductor Diameter - Maximum	0 in
Conductor Spacing	0 in

Logistics

Pallet Quantity	384
-----------------	-----

Product Assets

[Catalogs - Transmission Connectors Catalog - Full](#)
[Sales Drawings - 946693001 Drawing](#)
[Sales Drawings - 946693001 CUTSHEET](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
AN-946693001-SPEC-EN | REV 6/2024