


HUBBELL

Power Systems

Yoke Plate, Rectangular

By ANDERSON
Catalog # [950213002](#)

Rectangular configuration yoke plates are used with a double string of insulators to deadend a two conductor bundle.



Features

- Rectangular Configuration Yoke Plate
- Ultimate Strength is 50,000 lbs.
- 18" hole spacing
- 0.75" thickness
- Material: Galvanized Steel

General

Corona Ring Mounting Provision	4 x 0.500" Cap Screws
EU RoHS Indicator	No
Material	Steel
Number of Bolt Holes	0
Series	YPR Series
Strength Rating - Ultimate	50000 lb
Strength Rating - Ultimate Body	0 lb
UPC	096359253259

Dimensions

Assembly Rating (Ultimate)	0 lb
Diameter - Bolt	0 in
Diameter - Insulator Attachment Holes	0.938 in
Diameter - Pin	0 in
Dimensions	18 in x 8.25 in x 0.75 in
Height	0.75 in
Insulator / Conductor Hole Spacing	18 in
Insulator Throat Diameter - Maximum	0 in
Insulator Throat Diameter - Minimum	0 in
Length	18 in
Length - Coupling	5.5 in
Length - Pin	0 in
Maximum Adjustment	0 in
Ring Height	0 in
Thickness	0.75 in
Weight	44.443 lb
Width	8.25 in

Conductor Related

Conductor Diameter - Maximum	0 in
Conductor Spacing Diameter - Conductor Attachment Holes	0 in 0.813 in

Product Assets

[Catalogs - Transmission Connectors Catalog - Full Sales Drawings - 950213002 CUTSHEET](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
AN-950213002-SPEC-EN | REV 6/2024