

# HUBBELL

## Power Systems

### Yoke Plate, Rectangular

By ANDERSON  
Catalog # [976113002](#)

Rectangular configuration yoke plates are used with a double string of insulators to deadend a two conductor bundle.



#### Features

- Rectangular Configuration Yoke Plate
- Ultimate Strength is 30,000 lbs.
- 18" hole spacing
- 0.63" thickness
- Material: Galvanized Steel

#### General

Corona Ring Mounting Provision	4 x 0.500" Cap Screws
EU RoHS Indicator	No
Material	Steel
Number of Bolt Holes	0
Series	YPR Series
Strength Rating - Ultimate	30000 lb
Strength Rating - Ultimate Body	0 lb
UPC	096359253426

#### Dimensions

Assembly Rating (Ultimate)	0 lb
Diameter - Bolt	0 in
Diameter - Insulator Attachment Holes	0.688 in
Diameter - Pin	0 in
Dimensions	20.5 in x 8.5 in x 0.625 in
Height	0.625 in
Insulator / Conductor Hole Spacing	18 in
Insulator Throat Diameter - Maximum	0 in
Insulator Throat Diameter - Minimum	0 in
Length	20.5 in
Length - Coupling	6 in
Length - Pin	0 in
Maximum Adjustment	0 in
Ring Height	0 in
Thickness	0.625 in
Weight	29.4 lb
Width	8.5 in

#### Conductor Related

Conductor Diameter - Maximum	0 in
Conductor Spacing Diameter - Conductor Attachment Holes	0 in 0.938 in

#### Product Assets

[Catalogs - Transmission Connectors Catalog - Full Sales Drawings - 976113002 CUTSHEET](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
AN-976113002-SPEC-EN | REV 6/2024