

HUBBELL

Power Systems

Anchor Shackle - 100k lb

By ANDERSON
Catalog # [976743001](#)

Anchor Shackles are used to attach hardware to the tower pad. Back to back anchor shackles are commonly used at the tower attachment point to orient the plane of the tower plate and the balance of the insulator hardware.



Features

- Ultimate strength is 100,000 lbs. (445 kN)
- Opening Width: 1.688 inches
- Clevis Pin Diameter: 1.125 inches
- Material: Body - galvanized steel, Hardware - galvanized steel, Cotter Pin - stainless steel
- This shackle is type BNK (furnished with Bolt, Nut, and cotter Key).

General

Material	Steel
Material - Pin (Clevis)	Galvanized Steel
Material - Pin (Cotter)	Stainless Steel
Number of Bolt Holes	0
Series	AS Series
Strength Rating - Ultimate	100000 lb
Strength Rating - Ultimate	0 lb
Body	
UPC	096359253457

Dimensions

Assembly Rating (Ultimate)	0 lb
Clevis Opening	1.688 in
Diameter - Bolt	0 in
Diameter - Pin	0 in
Dimensions	6 in x 3.86 in x 2.38 in
Height	2.38 in
Insulator Throat Diameter - Maximum	0 in
Insulator Throat Diameter - Minimum	0 in
Insulator Throat Diameter Range	0 - 0
Length	6 in
Length - Coupling	4.313 in
Length - Pin	0 in
Maximum Adjustment	0 in
Ring Height	0 in
Weight	5.782 lb
Width	3.86 in

Conductor Related

Conductor Diameter - Maximum	0 in
Conductor Spacing	0 in

Logistics

Carton Quantity	6
Pallet Quantity	360

Product Assets

[Catalogs - Transmission Connectors Catalog - Full](#)
[Sales Drawings - 976743001 Drawing](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
AN-976743001-SPEC-EN | REV 6/2024