

## Yoke Plate, Triangular

By ANDERSON  
Catalog # [796034001](#)

Delta configuration yoke plates may be used to bundle two conductors in suspension application with a single string insulator. They may also be used in deadend applications with two strings of insulators and one deadend clamp.



### Features

- Delta Configuration Yoke Plate
- Ultimate Strength is 60,000 lbs.
- 13" hole spacing
- 0.75" thickness
- Material: Galvanized Steel

### General

EU RoHS Indicator	No
Material	Steel
Number of Bolt Holes	0
Series	YPD Series
Strength Rating - Ultimate	60000 lb
Strength Rating - Ultimate	0 lb
Body	
UPC	096359252290

### Dimensions

Assembly Rating (Ultimate)	0 lb
Base Hole Spacing	13 in
Diameter - Apex Hole	0.938 in
Diameter - Base Holes	1.063 in
Diameter - Bolt	0 in
Diameter - Pin	0 in
Insulator / Conductor Hole Spacing	13 in
Insulator Throat Diameter - Maximum	0 in
Insulator Throat Diameter - Minimum	0 in
Length - Coupling	3.438 in
Length - Pin	0 in
Maximum Adjustment	0 in
Ring Height	0 in
Thickness at Apex	0.75 in
Thickness at Base	0.75 in
Weight	0.412 lb

### Conductor Related

Conductor Diameter - Maximum	0 in
Conductor Spacing	0 in

### Logistics

Pallet Quantity	90
-----------------	----

### Product Assets

[Catalogs - Transmission Connectors Catalog - Full](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
AN-796034001-SPEC-EN | REV 6/2024