

HUBBELL

Power Systems

Deadend, Straight Line. Ductile, Copper, CopperWeld, Alumoweld. Conductor Range 0.46 - 0.86 in, Fitting: None

By ANDERSON
Catalog # [876722000](#)

Deadend, Straight Line. Ductile, Copper, CopperWeld, Alumoweld. Conductor Range 0.46 - 0.86 in.

Features

- For use with copper and CopperWeld phase conductor
- Magnetic induction heating will occur
- For dead ending static wire
- Add "S" for socket OR "C" for clevis fitting

General

Catalog Number	876722000
Fitting Type	None
Material	Ductile Iron; Steel
Material - Body	Ductile Iron
Material - Hardware	Galvanized Steel
Material - Keeper	Ductile Iron
Product Category	Straight Line
Strength Rating - Ultimate	10000 lb
Body	
Style	87600 - Deadend, Straight Line
Type	Bolted
U-Bolts	2 in
UPC	096359252559

Dimensions

Clevis Opening	0.75 in
Diameter - Bolt	0.5 in
Diameter - Pin	0.625 in
Length	9.25 in
Weight	4.1 lb
Width	0.75 in

Electrical Ratings

Voltage Application	Standard
---------------------	----------



*Representative Image

Conductor Related

Conductor Compatibility	ACSR-Turkey-6-6/1;ACSR-Pigeon-3/0-6/1;ACSR-Waxwing-266.8-18/1;ACSR-Partridge-266.8-26/7;ACSR-Ostrich-300-26/7;ACSR-Merlin-336.4-18/1;ACSR-Linnet-336.4-26/7;ACSR-Oriole-336.4-30/7;ACSR-Chickadee-397.5-18/1;ACSR-Brant-397.5-24/7;ACSR-Ibis-397.5-26/7;ACSR-Lark-397.5-30/7;ACSR-Pelican-477-18/1;ACSR-Flicker-477-24/7;ACSR-Hawk-477-26/7;ACSR-Brahma-203.2-16/19;AAC-Phlox-3/0-7;AAC-Oxlip-4/0-7;AAC-Valerian-250-19;AAC-Laurel-266.8-19;AAC-Daffodil-350-19;AAC-Canna-397.5-19;AAC-Cosmos-477-19;AAC-Syringa-477-37;AAC-Zinnia-500-19;AAC-Hyacinth-500-37;AAC-Dahlia-556.5-19;AAC-Mistletoe-556.5-37;AAAC 6201 Alloy-Amherst-195.7-6/18;AAAC 6201 Alloy-Alliance-246.9-6/18
Conductor Diameter - Maximum	0.86
Conductor Diameter - Minimum	0.46
Conductor Diameter Range	0.46 - 0.86

Logistics

Pallet Quantity	270
-----------------	-----

Product Assets

[Catalogs - Transmission Connectors Catalog - Full](#)
[Catalogs - Distribution Connectors](#)
[Literature - Ropes Course Industry Letter \(April 2021\)](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
AN-876722000-SPEC-EN | REV 6/2024