

Terminal, Aluminum Bolted

By ANDERSON
Catalog # [ACF11B2](#)

"Terminal, Bolted, Expansion Tube to Flat, Schedule 40 IPS, tube size: 1" IPS, 2-Hole Straight Pad, Material: Castings-Aluminum alloy, Factory formed laminated shunts-Aluminum, Clamping hardware-Aluminum alloy"



Features

- "Clamping bolts have hex-stops for one-wrench installation
- Contact sealant is recommended
- 90° pad orientation available, 45° pad orientation available"

General

Material	Aluminum
Material - Clamping Hardware	Aluminum Alloy
Number of Bolt Holes	2
Number of Pad Holes	2
Type	Bolted Lugs & Terminals
UPC	096359279037

Dimensions

Weight	1.307 lb
Width - Pad	2 in

Conductor Related

Conductor Compatibility	ACSR-Hen-477-30/7;ACSR-Osprey-556.5-18/1;ACSR-Parakeet-556.5-24/7;ACSR-Dove-556.5-26/7;ACSR-Eagle-556.5-30/7;ACSR-Peacock-605-24/7;ACSR-Squab-605-26/7;ACSR-Teal-605-30/19;ACSR-Kingbird-636-18/1;ACSR-Swift-636-36/1;ACSR-Rook-636-24/7;ACSR-Grosbeak-636-26/7;ACSR-Egret-636-30/19;ACSR-Flamingo-666.6-24/7;ACSR-Gannet-666.6-26/7;ACSR-Stilt-715.5-24/7;ACSR-Starling-715.5-26/7;ACSR-Redwing-715.5-30/19;ACSR-Coot-795-36/1;ACSR-Cuckoo-795-24/7;ACSR-Drake-795-26/7;ACSR-Tern-795-45/7;ACSR-Condor-795-54/7;AAC-Meadowsweet-600-37;AAC-Orchid-636-37;AAC-Flag-700-61;AAC-Violet-715.5-37;AAC-Nasturtium-715.5-61;AAC-Cattail-750-61;AAC-Arbutus-795-37;AAC-Lilac-795-61;AAC-Cockscomb-900-37;AAC-Snapdragon-900-61
Conductor Diameter - Maximum	1.108 in
Conductor Diameter - Minimum	0.87 in
Conductor Diameter Range	0.87 - 1.108
Conductor Type	<ul style="list-style-type: none"> • AAC • ACSR

Logistics

Pallet Quantity	1200
-----------------	------

Product Assets

[Catalogs - Substation Connectors \(SA\)](#)

[Sales Drawings - C-4183](#)

[Video - Hubbell Power Systems 3D Portal to help with developing 3D models of substation connector products \(VI05050E0619\)](#)

[Video - Hubbell Power Systems Quick Ship \(VI05124E1018\)](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
AN-ACF11B2-SPEC-EN | REV 1/2024