

# HUBBELL

## Power Systems

### Hold Down Shackle

By ANDERSON

Catalog # [880162000](#)

Hold down shackles are attached to suspension clamps to provide an attachment point to hook bolt or eye bolt.



#### Features

- Ultimate Strength is 10,000 lbs (44kN)
- Clevis Opening Width: 3.250 inches, Clevis pin diameter: 0.625 inches
- Supplied with Clevis Pin and Cotter Pin
- HDWC type circular hold down weights can be attached in the desired increments to provide a means of controlling conductor position by preventing excessive uplift and sway.
- Material: Body - forged steel, Clevis pin - galvanized steel, Cotter pin - stainless steel

#### General

EU RoHS Indicator	No
Material	Steel
Material - Pin (Clevis)	Galvanized Steel
Material - Pin (Cotter)	Stainless Steel
Number of Bolt Holes	0
Series	HDS Series
Strength Rating - Ultimate	10000 lb
Strength Rating - Ultimate	0 lb
Body	
UPC	096359252641

#### Dimensions

Assembly Rating (Ultimate)	0 lb
Diameter - Bolt	0 in
Diameter - Pin	0 in
Insulator Throat Diameter - Maximum	0 in
Insulator Throat Diameter - Minimum	0 in
Insulator Throat Diameter Range	0 - 0
Length - Coupling	6 in
Length - Pin	0 in
Maximum Adjustment	0 in
Ring Height	0 in
Weight	1.607 lb

#### Conductor Related

Conductor Diameter - Maximum	0 in
Conductor Spacing	0 in

#### Product Assets

[Catalogs - Transmission Connectors Catalog - Full Literature - Ropes Course Industry Letter \(April 2021\)](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
AN-880162000-SPEC-EN | REV 6/2024