

Terminal, Aluminum Bolted

By ANDERSON
Catalog # [ACF6C](#)

"Terminal, Bolted, Expansion Tube to Flat, Schedule 80 IPS, tube size: 1" EHIPS, 2-Hole Straight Pad, Material: Castings-Aluminum alloy, Factory formed laminated shunts-Aluminum, Clamping hardware-Aluminum alloy"



*Representative Image

Features

- "Clamping bolts have hex-stops for one-wrench installation
- Contact sealant is recommended
- 90° pad orientation available, 45° pad orientation available"

General

Material	Aluminum
Material - Clamping Hardware	Aluminum Alloy
Number of Bolt Holes	4
Number of Pad Holes	4
Type	Bolted Lugs & Terminals
UPC	096359279754

Dimensions

Angle - Pad	180 °
Weight	1.078 lb
Width - Pad	3 in

Conductor Related

Conductor Compatibility	ACSR-Swan-4-6/1;ACSR-Swanate-4-7/1;ACSR-Sparrow-2-6/1;ACSR-Sparate-2-7/1;ACSR-Robin-1-6/1;ACSR-Raven-1/0-6/1;ACSR-Quail-2/0-6/1;ACSR-Pigeon-3/0-6/1;ACSR-Penguin-4/0-6/1;AAC-Rose-4-7;AAC-Iris-2-7;AAC-Pansy-1-7;AAC-Poppy-1/0-7;AAC-Aster-2/0-7;AAC-Phlox-3/0-7;AAC-Oxlip-4/0-7;AAC-Valerian-250-19
Conductor Diameter - Maximum	0.575 in
Conductor Diameter - Minimum	0.232 in
Conductor Diameter Range	0.232 - 0.575
Conductor Type	<ul style="list-style-type: none">• AAC• ACSR

Product Assets

[Catalogs - Substation Connectors \(SA\)](#)

[Video - Hubbell Power Systems 3D Portal to help with developing 3D models of substation connector products \(VI05050E0619\)](#)

[Video - Hubbell Power Systems Quick Ship \(VI05124E1018\)](#)