

HUBBELL Power Systems

Socket Eye

By ANDERSON
Catalog # [909612000](#)

Socket eyes can be used for connecting conductor clamping devices to ball and socket type insulators.



*Representative Image

Features

- Ultimate Strength is 50,000 lbs. (222 kN)
- Hole Diameter - 0.813 inches
- Width - 1-1/2"
- Length - 5-1/2"
- Material: Body - galvanized ductile iron, Cotter Pin - stainless steel
- For use with ANSI class 52-8 and 52-11 insulators per ANSI Spec. C29.2-71.

General

EU RoHS Indicator	No
Material	Ductile Iron
Material - Pin (Cotter)	Stainless Steel
Number of Bolt Holes	0
Series	SA Series
Strength Rating - Ultimate	50000 lb
Strength Rating - Ultimate	0 lb
Body	
UPC	096359252818

Dimensions

Assembly Rating (Ultimate)	0 lb
Diameter - Bolt	0 in
Diameter - Eye Hole	0.813 in
Diameter - Pin	0 in
Dimensions	7.25 in x 1.5 in x 1.531 in
Height	1.531 in
Insulator Throat Diameter - Maximum	0 in
Insulator Throat Diameter - Minimum	0 in
Insulator Throat Diameter Range	0 - 0
Length	7.25 in
Length - Coupling	5.5 in
Length - Pin	0 in
Maximum Adjustment	0 in
Ring Height	0 in
Weight	5.88 lb
Width	1.5 in
Width - Eye	1.5 in

Conductor Related

Conductor Diameter - Maximum	0 in
Conductor Spacing	0 in

Logistics

Pallet Quantity	384
-----------------	-----

Product Assets

[Catalogs - Transmission Connectors Catalog - Full](#)
[Sales Drawings - 90961-2000 CUT SHEET](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
AN-909612000-SPEC-EN | REV 6/2024