

Terminal, Aluminum Bolted

By ANDERSON
Catalog # [ACF9B2](#)

"Terminal, Bolted, Expansion Tube to Flat, Schedule 80 IPS, tube size: 2" EHIPS, 2-Hole Straight Pad, Material: Castings-Aluminum alloy, Factory formed laminated shunts-Aluminum, Clamping hardware-Aluminum alloy"



Features

- "Clamping bolts have hex-stops for one-wrench installation
- Contact sealant is recommended
- 90° pad orientation available, 45° pad orientation available"

General

Material	Aluminum
Material - Clamping Hardware	Aluminum Alloy
Number of Bolt Holes	2
Number of Pad Holes	2
Type	Bolted Lugs & Terminals
UPC	096359279990

Dimensions

Angle - Pad	180 °
Dimensions	2.688 in x 6.5 in x 1.313 in
Height	1.313 in
Length	2.688 in
Weight	1.198 lb
Width	6.5 in
Width - Pad	2 in

Conductor Related

Conductor Compatibility	ACSR-Merlin-336.4-18/1;ACSR-Linnet-336.4-26/7;ACSR-Oriole-336.4-30/7;ACSR-Chickadee-397.5-18/1;ACSR-Brant-397.5-24/7;ACSR-Ibis-397.5-26/7;ACSR-Lark-397.5-30/7;ACSR-Pelican-477-18/1;ACSR-Flicker-477-24/7;ACSR-Hawk-477-26/7;ACSR-Hen-477-30/7;ACSR-Osprey-556.5-18/1;ACSR-Brahma-203.2-16/19;AAC-Canna-397.5-19;AAC-Cosmos-477-19;AAC-Syringa-477-37;AAC-Zinnia-500-19;AAC-Hyacinth-500-37;AAC-Dahlia-556.5-19;AAC-Mistletoe-556.5-37;AAC-Meadowsweet-600-37
Conductor Diameter - Maximum	0.893 in
Conductor Diameter - Minimum	0.681 in
Conductor Diameter Range	0.681 - 0.893
Conductor Type	<ul style="list-style-type: none"> • AAC • ACSR

Logistics

Pallet Quantity	1008
-----------------	------

Product Assets

[Catalogs - Substation Connectors \(SA\)](#)
[Sales Drawings - C-4183](#)

[Video - Hubbell Power Systems 3D Portal to help with developing 3D models of substation connector products \(VI05050E0619\)](#)

[Video - Hubbell Power Systems Quick Ship \(VI05124E1018\)](#)