

Stud Connector, Aluminum

By ANDERSON
Catalog # [ADSC0679016](#)

"Bolted Stud Connectors, Connecting Stud to Cable, Stud Dia./Thd.- 1-1/2"-12, Conductor Range: AAC-1500-2000 MCM, ACSR- 1272-1590 MCM, Dia.- 1.382"-1.632", Material: Castings- Aluminum Alloy, Hardware- Aluminum Alloy"



*Representative Image

Features

- 0

General

Material	Aluminum
Material - Clamping Hardware	Aluminum Alloy
Number of Stud Threads	16
Type	Stud to Cable

Dimensions

Angle - Stud to Conductor	90 °
Diameter - Stud	3.75 in
Weight	1.100 lb

Conductor Related

Conductor Compatibility	ACSR-Penguin-4/0-6/1;ACSR-Waxwing-266.8-18/1;ACSR-Partridge-266.8-26/7;ACSR-Ostrich-300-26/7;ACSR-Merlin-336.4-18/1;ACSR-Linnet-336.4-26/7;ACSR-Oriole-336.4-30/7;ACSR-Chickadee-397.5-18/1;ACSR-Brahma-203.2-16/19;AAC-Valerian-250-19;AAC-Laurel-266.8-19;AAC-Daffodil-350-19;AAC-Canna-397.5-19
Conductor Diameter - Maximum	0.744 in
Conductor Diameter - Minimum	0.563 in
Conductor Diameter Range	0.563 - 0.744
Conductor Type	<ul style="list-style-type: none"> • AAC • ACSR

Product Assets

[Catalogs - Substation Connectors \(SA\)](#)

[Video - Hubbell Power Systems 3D Portal to help with developing 3D models of substation connector products \(VI05050E0619\)](#)

[Video - Hubbell Power Systems Quick Ship \(VI05124E1018\)](#)