

## Socket Eye

By ANDERSON  
Catalog # [909662000](#)

Socket Eye, Ductile Iron, Eye: 1.063" width with 1.063" Hole, Length: 5.5", UTS 50,000 lb- For use with ANSI class 52-8 & 52-11 insulators. SOCKET, EYE DI 50K A52-11 W1.06 D17/16 L



\*Representative Image

### Features

- For use with ANSI class 52-8 & 52-11 insulators

### General

EU RoHS Indicator	No
Material	Ductile Iron
Material - Pin (Cotter)	Stainless Steel
Series	SA Series
Strength Rating - Ultimate	50000 lb
UPC	096359252832

### Dimensions

Diameter - Eye Hole	1.063 in
Insulator Throat Diameter Range	0 - 0
Length - Coupling	5.5 in
Weight	5.684 lb
Width - Eye	1.063 in

### Logistics

Pallet Quantity	320
-----------------	-----

### Product Assets

[Catalogs - Transmission Connectors Catalog - Full \(CA05063E\)](#)