

# HUBBELL

## Power Systems

### Yoke Plate, Dual-Bundle

By ANDERSON

Catalog # [930064004](#)

Vee configuration yoke plates are used with a VEE string of insulators to attach a two conductor bundle.



#### Features

- Vee Configuration Yoke Plate
- Ultimate Strength is 40,000 lbs.
- 18" hole spacing
- 0.75" thickness
- Material: Galvanized Steel

#### General

EU RoHS Indicator	No
Material	Steel
Number of Bolt Holes	0
Series	YPV Series
Strength Rating - Ultimate	40000 lb
Strength Rating - Ultimate Body	0 lb
UPC	096359252931

#### Dimensions

Assembly Rating (Ultimate)	0 lb
Diameter - Bolt	0 in
Diameter - Insulator Attachment Holes	1.25 in
Diameter - Pin	0 in
Insulator / Conductor Hole Spacing	18 in
Insulator Throat Diameter - Maximum	0 in
Insulator Throat Diameter - Minimum	0 in
Length	20.75 in
Length - Coupling	7.071 in
Length - Pin	0 in
Maximum Adjustment	0 in
Ring Height	0 in
Thickness	0.75 in
Weight	26.46 lb

#### Conductor Related

Conductor Diameter - Maximum	0 in
Conductor Spacing Diameter - Conductor Attachment Holes	0 in 1.25 in

#### Logistics

Pallet Quantity	85
-----------------	----

#### Product Assets

[Catalogs - Transmission Connectors Catalog - Full Sales Drawings - 93006-4004 CUTSHEET](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
AN-930064004-SPEC-EN | REV 6/2024