

Stud Connector, Aluminum

By ANDERSON
Catalog # [ADSC12119012](#)

"Bolted Stud Connectors, Connecting Stud to Cable, Stud Dia./Thd.- 2"-12, Conductor Range: AAC- 350-600 MCM, ACSR- 336.4-477 MCM, Dia.-0.681"-0.893", Material: Castings- Aluminum Alloy, Hardware- Aluminum Alloy"



*Representative Image

Features

- 0

General

Material	Aluminum
Material - Clamping Hardware	Aluminum Alloy
Number of Stud Threads	12
Type	Stud to Cable

Dimensions

Angle - Stud to Conductor	90 °
Diameter - Stud	1.25 in
Weight	1.900 lb

Conductor Related

Conductor Compatibility	ACSR-Hen-477-30/7;ACSR-Osprey-556.5-18/1;ACSR-Parakeet-556.5-24/7;ACSR-Dove-556.5-26/7;ACSR-Eagle-556.5-30/7;ACSR-Peacock-605-24/7;ACSR-Squab-605-26/7;ACSR-Teal-605-30/19;ACSR-Kingbird-636-18/1;ACSR-Swift-636-36/1;ACSR-Rook-636-24/7;ACSR-Grosbeak-636-26/7;ACSR-Egret-636-30/19;ACSR-Flamingo-666.6-24/7;ACSR-Gannet-666.6-26/7;ACSR-Stilt-715.5-24/7;ACSR-Starling-715.5-26/7;ACSR-Redwing-715.5-30/19;ACSR-Coot-795-36/1;ACSR-Cuckoo-795-24/7;ACSR-Drake-795-26/7;ACSR-Tern-795-45/7;ACSR-Condor-795-54/7;AAC-Meadowsweet-600-37;AAC-Orchid-636-37;AAC-Flag-700-61;AAC-Violet-715.5-37;AAC-Nasturtium-715.5-61;AAC-Cattail-750-61;AAC-Arbutus-795-37;AAC-Lilac-795-61;AAC-Cockscomb-900-37;AAC-Snapdragon-900-61
Conductor Diameter - Maximum	1.108 in
Conductor Diameter - Minimum	0.87 in
Conductor Diameter Range	0.87 - 1.108
Conductor Type	<ul style="list-style-type: none"> • AAC • ACSR

Product Assets

[Catalogs - Substation Connectors \(SA\)](#)

[Video - Hubbell Power Systems 3D Portal to help with developing 3D models of substation connector products \(VI05050E0619\)](#)

[Video - Hubbell Power Systems Quick Ship \(VI05124E1018\)](#)



A proud member of the Hubbell Family.