

# HUBBELL

## Power Systems

### Yoke Plate, Triangular

By ANDERSON

Catalog # [951544001](#)

Delta configuration yoke plates may be used to bundle two conductors in suspension application with a single string insulator. They may also be used in deadend applications with two strings of insulators and one deadend clamp.



#### Features

- Delta Configuration Yoke Plate
- Ultimate Strength is 100,000 lbs.
- 18" hole spacing
- 0.88" thickness
- Material: Galvanized Steel

#### General

EU RoHS Indicator	No
Material	Steel
Number of Bolt Holes	0
Series	YPD Series
Strength Rating - Ultimate	100000 lb
Strength Rating - Ultimate Body	0 lb
UPC	096359253273

#### Dimensions

Assembly Rating (Ultimate)	0 lb
Base Hole Spacing	18 in
Diameter - Apex Hole	1.25 in
Diameter - Base Holes	0.938 in
Diameter - Bolt	0 in
Diameter - Pin	0 in
Dimensions	20.75 in x 10 in x 0.88 in
Height	0.88 in
Insulator / Conductor Hole Spacing	18 in
Insulator Throat Diameter - Maximum	0 in
Insulator Throat Diameter - Minimum	0 in
Length	20.75 in
Length - Coupling	6.125 in
Length - Pin	0 in
Maximum Adjustment	0 in
Ring Height	0 in
Thickness at Apex	0.875 in
Thickness at Base	0.875 in
Weight	33.075 lb
Width	10 in

#### Conductor Related

Conductor Diameter - Maximum	0 in
Conductor Spacing	0 in

#### Logistics

Pallet Quantity	66
-----------------	----

#### Product Assets

[Catalogs - Transmission Connectors Catalog - Full Sales Drawings - 951544001 CUTSHEET](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
AN-951544001-SPEC-EN | REV 6/2024