

HUBBELL Power Systems

Cable Spacer, Aluminum

By ANDERSON
Catalog # [APCS1612](#)

Aluminum Alloy, parallel cable spacer for maintaining aluminum cable clearance and preventing loose cable damage.



*Representative Image

Features

- 12 in Spacing
- Conductor Diameter Ranges: 1.382 - 1.632 inches
- Conductor Ranges: 1500 - 2000 MCM AAC and 1272 - 1590 MCM ACSR
- Material: Casting - 356-T6 aluminum alloy, Hardware - aluminum alloy
- Contact sealant is recommended.
- Recommended for slack spans only.
- For substation use only. Do not use for overhead transmission lines.

General

EU RoHS Indicator	No
Material	Aluminum
Material - Clamping Hardware	Aluminum Alloy
Number of Ground Braid Lug Holes	0
Type	Cable Spacer
UPC	096359283782

Dimensions

Base Hole Spacing	0 in
Diameter - Base Holes	0 in
Diameter - Bolt	0 in
Diameter - Inside	0 in
Length - Coupling	0 in
Length Before Compression	0 in
Weight	4.116 lb

Electrical Ratings

Maximum Current Rating Amps 0
Continuous

Conductor Related

Conductor Compatibility	ACSR-Pheasant-1272-54/19;ACSR-Dipper-1351.5-45/7;ACSR-Martin-1351.5-54/19;ACSR-Bobolink-1431-45/7;ACSR-Plover-1431-54/19;ACSR-Nuthatch-1510.5-45/7;ACSR-Parrot-1510.5-54/19;ACSR-Lapwing-1590-45/7;ACSR-Falcon-1590-54/19;ACSR-Chukar-1780-84/19;AAC-Gladiolus-1510.5-61;AAC-Coreopsis-1590-61;AAC-Cowslip-2000-91
Conductor Diameter - Maximum	1.632 in
Conductor Diameter - Minimum	1.382 in
Conductor Diameter Range	1.382 - 1.632
Conductor Spacing	12 in
Conductor Type	AAC ACSR

Product Assets

[Catalogs - Substation Connectors \(SA\)](#)
[Sales Drawings - C-4936 \(APCS Product Family\)](#)
[Video - Hubbell Power Systems 3D Portal to help with developing 3D models of substation connector products](#)
[Video - Hubbell Power Systems Quick Ship](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
AN-APCS1612-SPEC-EN | REV 6/2024