

# HUBBELL

## Power Systems

### Anchor Shackle - 60k lb

By ANDERSON  
Catalog # [970303002](#)

Anchor Shackles are used to attach hardware to the tower pad. Back to back anchor shackles are commonly used at the tower attachment point to orient the plane of the tower plate and the balance of the insulator hardware.



#### Features

- Ultimate strength is 60,000 lbs. (267 kN)
- Opening Width: 1.125 inches
- Bolt Diameter: 0.750 inches
- This shackle is type BNK which is furnished with Bolt, Nut and Cotter Key
- Material: Body - galvanized steel, Hardware - galvanized steel, Cotter Pin - stainless steel

#### General

Material	Steel
Material - Pin (Clevis)	Galvanized Steel
Material - Pin (Cotter)	Stainless Steel
Number of Bolt Holes	0
Series	AS Series
Strength Rating - Ultimate	60000 lb
Strength Rating - Ultimate	0 lb
Body	
UPC	096359253334

#### Dimensions

Assembly Rating (Ultimate)	0 lb
Clevis Opening	1.125 in
Diameter - Bolt	0 in
Diameter - Pin	0 in
Dimensions	5.625 in x 3.313 in x 0.75 in
Height	0.75 in
Insulator Throat Diameter - Maximum	0 in
Insulator Throat Diameter - Minimum	0 in
Insulator Throat Diameter Range	0 - 0
Length	5.625 in
Length - Coupling	5 in
Length - Pin	0 in
Maximum Adjustment	0 in
Ring Height	0 in
Weight	2.233 lb
Width	3.313 in

#### Conductor Related

Conductor Diameter - Maximum	0 in
Conductor Spacing	0 in

#### Logistics

Pallet Quantity	720
-----------------	-----

#### Product Assets

[Catalogs - Transmission Connectors Catalog - Full Sales Drawings - 970303002 CUTSHEET](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
AN-970303002-SPEC-EN | REV 6/2024