

## Coupler, Aluminum Bolted

By ANDERSON  
Catalog # [ASTC147](#)

Coupler, Straight, Tube to Cable, Aluminum Bolted, 1-1/2  
IPS/EHIPS tube to 0.563 - 0.744 cable. COUPLER, AL 1.5 IPS  
TO .563-.744 IN



\*Representative Image

### Features

- "Coupler, Straight, Tube to Cable, Aluminum Bolted, 1-1/2" IPS/EHIPS tube to 0.563"-0.744" dia. cable, Material: Castings-Aluminum alloy, Hardware-Aluminum alloy"

### General

Bolt Installation Torque (Recommended)	300 in-lbs
EU RoHS Indicator	No
Material	Aluminum
Material - Clamping Hardware	Aluminum Alloy
Type	Tube to Cable Couplers
UPC	096359347941

### Dimensions

Diameter - Clamping Hardware	0.5 in
Diameter - Rod / Tube	1-1/2 in
Weight	1.274 lb

### Electrical Ratings

Maximum Current Rating Amps Continuous	See Technical Advisor
--	-----------------------

### Conductor Related

Conductor Compatibility	ACSR-Penguin-4/0-6/1;ACSR-Waxwing-266.8-18/1;ACSR-Partridge-266.8-26/7;ACSR-Ostrich-300-26/7;ACSR-Merlin-336.4-18/1;ACSR-Linnet-336.4-26/7;ACSR-Oriole-336.4-30/7;ACSR-Chickadee-397.5-18/1;ACSR-Brahma-203.2-16/19;AAC-Valerian-250-19;AAC-Laurel-266.8-19;AAC-Tulip-336.1-19;AAC-Daffodil-350-19;AAC-Canna-397.5-19
Conductor Diameter (Tap) - Maximum	0.744 in
Conductor Diameter (Tap) - Minimum	0.563 in
Conductor Type	Aluminum Bus

### Logistics

Pallet Quantity	432
-----------------	-----

### Product Assets

[Catalogs - Substation Connectors \(SA\)](#)

[Sales Drawings - C-1488 \(ASTC Product Family\)](#)

[Video - Hubbell Power Systems 3D Portal to help with developing 3D models of substation connector products \(VI05050E0619\)](#)

[Video - Hubbell Power Systems Quick Ship \(VI05124E1018\)](#)