


HUBBELL

Power Systems

Yoke Plate, Triangular

By ANDERSON
Catalog # [971114001](#)

Delta configuration yoke plates may be used to bundle two conductors in suspension application with a single string insulator. They may also be used in deadend applications with two strings of insulators and one deadend clamp.



Features

- Delta Configuration Yoke Plate
- Ultimate Strength is 80,000 lbs.
- 18" hole spacing
- 0.75" thickness
- Material: Galvanized Steel A514 Grade B

General

EU RoHS Indicator	No
Material	Steel
Number of Bolt Holes	0
Series	YPD Series
Strength Rating - Ultimate	72000 lb
Strength Rating - Ultimate	0 lb
Body	
UPC	096359253341

Dimensions

Assembly Rating (Ultimate)	0 lb
Base Hole Spacing	18 in
Diameter - Apex Hole	1 in
Diameter - Base Holes	1 in
Diameter - Bolt	0 in
Diameter - Pin	0 in
Insulator / Conductor Hole Spacing	18 in
Insulator Throat Diameter - Maximum	0 in
Insulator Throat Diameter - Minimum	0 in
Length - Coupling	4 in
Length - Pin	0 in
Maximum Adjustment	0 in
Ring Height	0 in
Thickness at Apex	1.125 in
Thickness at Base	0.75 in
Weight	20.041 lb

Conductor Related

Conductor Diameter - Maximum	0 in
Conductor Spacing	0 in

Logistics

Pallet Quantity	384
-----------------	-----

Product Assets

[Catalogs - Transmission Connectors Catalog - Full](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
AN-971114001-SPEC-EN | REV 6/2024