

# HUBBELL

## Power Systems

### Tee, Aluminum Bolted

By ANDERSON  
Catalog # [ATCC77](#)



Aluminum alloy, cable to cable tee for connecting aluminum-aluminum or aluminum-copper conductor combinations. Clamping bolts have hex stops for one wrench installation. Contact sealant is recommended.

#### Features

- Tee, Aluminum Bolted, Cable to Cable
- MAIN: 4/0-336.4 MCM ACSR (0.563-0.744 inch dia.), TAP: 4/0-336.4 MCM ACSR (0.563-0.744 inch dia.)
- Castings are 356-T6 Aluminum Alloy
- Clamping Hardware is Aluminum Alloy
- Clamping bolts have hex-stops for one-wrench installation
- Cable contact inhibitor is recommended

#### General

Material	Aluminum
Material - Clamping Hardware	Aluminum Alloy
Number of Ground Braid Lug Holes	0
Type	Tee, Bolted
UPC	096359286998

#### Dimensions

Base Hole Spacing	0 in
Diameter - Base Holes	0 in
Diameter - Bolt	0 in
Diameter - Inside	0 in
Length - Coupling	0 in
Length Before Compression	0 in
Weight	0.98 lb

#### Electrical Ratings

Maximum Current Rating Amps 0  
Continuous

#### Conductor Related

Conductor Compatibility	ACSR-Penguin-4/0-6/1;ACSR-Waxwing-266.8-18/1;ACSR-Partridge-266.8-26/7;ACSR-Ostrich-300-26/7;ACSR-Merlin-336.4-18/1;ACSR-Linnet-336.4-26/7;ACSR-Oriole-336.4-30/7;ACSR-Chickadee-397.5-18/1;ACSR-Brahma-203.2-16/19;AAC-Valerian-250-19;AAC-Laurel-266.8-19;AAC-Tulip-336.1-19;AAC-Daffodil-350-19;AAC-Canna-397.5-19
Conductor Diameter (Main) - Maximum	0.744 in
Conductor Diameter (Main) - Minimum	0.563 in
Conductor Diameter (Main) Range	0.563 - 0.744
Conductor Diameter (Tap) - Maximum	0.744 in
Conductor Diameter (Tap) - Minimum	0.563 in
Conductor Type	AAC ACSR

#### Logistics

Pallet Quantity	504
-----------------	-----

#### Product Assets

- [Catalogs - Substation Connectors \(SA\)](#)
- [Video - Hubbell Power Systems 3D Portal to help with developing 3D models of substation connector products](#)
- [Video - Hubbell Power Systems Quick Ship](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
AN-ATCC77-SPEC-EN | REV 6/2024