

# HUBBELL

## Power Systems

### Anchor Shackle - 120k lb

By ANDERSON  
Catalog # [974153001](#)

Anchor Shackles are used to attach hardware to the tower pad. Back to back anchor shackles are commonly used at the tower attachment point to orient the plane of the tower plate and the balance of the insulator hardware.



#### Features

- Ultimate strength is 120,000 lbs. (534 kN)
- Opening Width: 1.500 inches
- Bolt Diameter: 1.250 inches
- This shackle is type BNK which is furnished with Bolt, Nut and Cotter Key
- Material: Body - galvanized steel, Hardware - galvanized steel, Cotter Pin - stainless steel

#### General

EU RoHS Indicator	No
Material	Steel
Material - Pin (Clevis)	Galvanized Steel
Material - Pin (Cotter)	Stainless Steel
Number of Bolt Holes	0
Series	AS Series
Strength Rating - Ultimate	120000 lb
Strength Rating - Ultimate Body	0 lb
UPC	096359253372

#### Dimensions

Assembly Rating (Ultimate)	0 lb
Clevis Opening	1.5 in
Diameter - Bolt	0 in
Diameter - Pin	0 in
Insulator Throat Diameter - Maximum	0 in
Insulator Throat Diameter - Minimum	0 in
Insulator Throat Diameter Range	0 - 0
Length	3.5 in
Length - Coupling	6 in
Length - Pin	0 in
Maximum Adjustment	0 in
Ring Height	0 in
Weight	6.86 lb
Width	6 in

#### Conductor Related

Conductor Diameter - Maximum	0 in
Conductor Spacing	0 in

#### Product Assets

[Catalogs - Transmission Connectors Catalog - Full](#)  
[Sales Drawings - 974153001 CUTSHEET](#)  
[Sales Drawings - 974153001 Drawing](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
AN-974153001-SPEC-EN | REV 6/2024