

Tee, Aluminum Bolted

By ANDERSON
Catalog # [ATCF18401](#)

Tee, Aluminum Bolted, Cable to Flat, MAIN: 2000-2500 MCM AAC (1.632-1.824 in. dia.), TAP: 4x4 in. w/ 4 hole (NEMA D size pad)



*Representative Image

Features

- Castings are 356-T6 Aluminum Alloy
- Clamping Hardware is Aluminum Alloy
- Pads are 3/8" thick
- Contact inhibitor is recommended

General

EU RoHS Indicator	No
Material	Aluminum
Material - Clamping Hardware	Aluminum Alloy
Number of Pad Holes	4
Type	Tee, Bolted
UPC	096359287148

Dimensions

Weight	4.018 lb
Width - Flat Bar Tap	4 in

Conductor Related

Conductor Compatibility	ACSR-Bluebird-2156-84/19;ACSR-Kiwi-2167-72/7;ACSR-Thrasher-2312-76/19;AAC-Sagebrush-2250-91;AAC-Lupine-2500-91
Conductor Diameter (Main) - Maximum	1.824 in
Conductor Diameter (Main) - Minimum	1.632 in
Conductor Diameter (Main) Range	1.632 - 1.824
Conductor Type	<ul style="list-style-type: none">• AAC• ACSR

Product Assets

[Catalogs - Substation Connectors \(SA\)](#)

[Sales Drawings - C-7148 \(ATCF Product Family\)](#)

[Video - Hubbell Power Systems 3D Portal to help with developing 3D models of substation connector products \(VI05050E0619\)](#)

[Video - Hubbell Power Systems Quick Ship \(VI05124E1018\)](#)