

# HUBBELL Power Systems

## Tee, Aluminum Bolted

By ANDERSON

Catalog # [ATT2C3013](#)

Aluminum alloy, tubing to double cable, tee for connecting aluminum-aluminum or aluminum-copper conductor combinations. Clamping bolts have hex-stops for one wrench installation. Contact sealent recommended.



\*Representative Image

### Features

- Tee, Aluminum Bolted, Tube to Two Cables, 3 IPS/EHIPS to 1.081-1.293" diameter double cable taps
- Material: Castings - 356-T6 aluminum alloy, Hardware - aluminum alloy.

### General

EU RoHS Indicator	No
Material	Aluminum
Material - Clamping Hardware	Aluminum Alloy
Number of Ground Braid Lug	0
Holes	
Type	Tee, Bolted
UPC	096359288053

### Dimensions

Base Hole Spacing	0 in
Diameter - Base Holes	0 in
Diameter - Bolt	0 in
Diameter - Inside	0 in
Length - Coupling	0 in
Length Before Compression	0 in
Weight	7.35 lb

### Electrical Ratings

Maximum Current Rating Amps Continuous	0
---	---

### Conductor Related

Conductor Compatibility	ACSR-Redwing-715.5-30/19;ACSR-Cuckoo-795-24/7;ACSR-Drake-795-26/7;ACSR-Condor-795-54/7;ACSR-Mallard-795-30/19;ACSR-Ruddy-900-45/7;ACSR-Canary-900-54/7;ACSR-Rail-954-45/7;ACSR-Cardinal-954-54/7;ACSR-Ortolan-1033.5-45/7;ACSR-Curlew-1033.5-54/7;ACSR-Bluejay-1113-45/7;ACSR-Finch-1113-54/19;AAC-Cockscomb-900-37;AAC-Snapdragon-900-61;AAC-Magnolia-954-37;AAC-Goldenrod-954-61;AAC-Camellia-1000-61;AAC-Bluebell-1033.5-37;AAC-Larkspur-1033.5-61;AAC-Marigold-1113-61;AAC-Hawthorn-1192.5-61
Conductor Diameter (Tap) - Maximum	1.293 in
Conductor Diameter (Tap) - Minimum	1.081 in
Conductor Type	Aluminum Bus

### Product Assets

[Catalogs - Substation Connectors \(SA\)](#)

[Sales Drawings - C-1753 \(ATT2 Product Family\)](#)

[Video - Hubbell Power Systems 3D Portal to help with developing 3D models of substation connector products](#)

[Video - Hubbell Power Systems Quick Ship](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
AN-ATT2C3013-SPEC-EN | REV 6/2024