

Cable Spacer, Aluminum

By ANDERSON
Catalog # [APCS98](#)

Aluminum Alloy, parallel cable spacer for maintaining aluminum cable clearance and preventing loose cable damage.



*Representative Image

Features

- 8 in Spacing
- Conductor Diameter Ranges: 0.681 - 0.893 inches
- Conductor Ranges: 350 - 600 MCM AAC and 336.4 - 477 MCM ACSR
- Material: Casting - 356-T6 aluminum alloy, Hardware - aluminum alloy
- Contact sealant is recommended.
- Recommended for slack spans only.
- For substation use only. Do not use for overhead transmission lines.

General

Catalog Number	APCS98
EU RoHS Indicator	No
Material	Aluminum
Material - Clamping Hardware	Aluminum Alloy
Number of Ground Braid Lug	0
Holes	
Type	Cable Spacer
UPC	096359283881

Dimensions

Base Hole Spacing	0 in
Diameter - Base Holes	0 in
Diameter - Bolt	0 in
Diameter - Inside	0 in
Length - Coupling	0 in
Length Before Compression	0 in
Weight	1.764 lb

Electrical Ratings

Maximum Current Rating Amps	0
Continuous	

Conductor Related

Conductor Compatibility	ACSR-Merlin-336.4-18/1;ACSR-Linnet-336.4-26/7;ACSR-Oriole-336.4-30/7;ACSR-Chickadee-397.5-18/1;ACSR-Brant-397.5-24/7;ACSR-Ibis-397.5-26/7;ACSR-Lark-397.5-30/7;ACSR-Pelican-477-18/1;ACSR-Flicker-477-24/7;ACSR-Hawk-477-26/7;ACSR-Hen-477-30/7;ACSR-Osprey-556.5-18/1;ACSR-Brahma-203.2-16/19;AAC-Canna-397.5-19;AAC-Cosmos-477-19;AAC-Syringa-477-37;AAC-Zinnia-500-19;AAC-Hyacinth-500-37;AAC-Dahlia-556.5-19;AAC-Mistletoe-556.5-37;AAC-Meadowsweet-600-37
Conductor Diameter - Maximum	0.893 in
Conductor Diameter - Minimum	0.681 in
Conductor Diameter Range	0.681 - 0.893
Conductor Spacing	8 in
Conductor Type	• AAC • ACSR

Certifications And Compliance

Buy America(n) Qualified	Contact Manufacturer
--------------------------	----------------------

Product Assets

- [Catalogs - Substation Connectors \(SA\)](#)
- [Sales Drawings - C-4936 \(APCS Product Family\)](#)
- [Specifications - APCS98](#)
- [Video - Hubbell Power Systems 3D Portal to help with developing 3D models of substation connector products](#)
- [Video - Hubbell Power Systems Quick Ship](#)