

Cable Spacer, Bronze

By ANDERSON
Catalog # [BPCS08012](#)



Bronze Cable Spacer, 12 in Spacing, Copper cable range 0.811 - 1.031 inches (500-800 MCM)

Features

- Recommended for slack spans only

General

EU RoHS Indicator	No
Material	Bronze
Material - Clamping Hardware	Stainless Steel
Number of Ground Braid Lug Holes	0
Type	Cable Spacer
UPC	096359292104

Dimensions

Base Hole Spacing	0 in
Diameter - Base Holes	0 in
Diameter - Bolt	0 in
Diameter - Inside	0 in
Length - Coupling	0 in
Length Before Compression	0 in
Weight	5.880 lb

Electrical Ratings

Maximum Current Rating Amps Continuous	0
--	---

Conductor Related

Conductor Diameter - Maximum	1.031 in
Conductor Diameter - Minimum	0.811 in
Conductor Diameter Range	0.811 - 1.031
Conductor Spacing	12 in
Conductor Type	Copper

Product Assets

- [Catalogs - Substation Connectors \(SA\)](#)
- [Sales Drawings - C-12901 \(BPCS Product Family\)](#)
- [Video - Hubbell Power Systems 3D Portal to help with developing 3D models of substation connector products \(VI05050E0619\)](#)
- [Video - Hubbell Power Systems Quick Ship \(VI05124E1018\)](#)