

Cable Spacer, Bronze

By ANDERSON
Catalog # [BPCS0806](#)



Bronze alloy, parallel cable spacer for maintaining cable clearance and preventing loose cable damage. Recommended for slack spans only.

*Representative Image

Features

- Bronze Cable Spacer, 6 in Spacing, Copper cable range 0.811 - 1.031 inches (500-800 MCM)
- Recommended for slack spans only
- Material: Casting - bronze alloy, Hardware - Stainless Steel

General

Catalog Number	BPCS0806
EU RoHS Indicator	No
Material	Bronze
Material - Clamping Hardware	Stainless Steel
Number of Ground Braid Lug Holes	0
Type	Cable Spacer
UPC	096359292135

Dimensions

Base Hole Spacing	0 in
Diameter - Base Holes	0 in
Diameter - Bolt	0 in
Diameter - Inside	0 in
Length - Coupling	0 in
Length Before Compression	0 in
Weight	5.488 lb

Electrical Ratings

Maximum Current Rating Amps 0
Continuous

Conductor Related

Conductor Diameter - Maximum	1.031 in
Conductor Diameter - Minimum	0.811 in
Conductor Diameter Range	0.811 - 1.031
Conductor Spacing	6 in
Conductor Type	Copper

Certifications And Compliance

Buy America(n) Qualified Contact Manufacturer

Product Assets

- [Catalogs - Substation Connectors \(SA\)](#)
- [Sales Drawings - C-12901 \(BPCS Product Family\)](#)
- [Specifications - BPCS0806](#)
- [Video - Hubbell Power Systems 3D Portal to help with developing 3D models of substation connector products](#)
- [Video - Hubbell Power Systems Quick Ship](#)