

## Cable Spacer, Aluminum w/ Pad

By ANDERSON  
Catalog # [APCSF9D8](#)

Cable Spacer, Aluminum, 8 in Spacing, range 0.681 - 0.893 inches (336.4-477 MCM ACSR), with 4-hole, 4 in terminal



\*Representative Image

### Features

- Recommended for slack spans only
- Contact sealant is recommended
- For limited current use like lightning arrester tap

### General

EU RoHS Indicator	No
Material	Aluminum
Material - Clamping Hardware	Aluminum Alloy
Type	Cable Spacer
UPC	096359284031

### Dimensions

Angle - Pad	180 °
Weight	2.646 lb
Width - Pad	4 in

### Conductor Related

Conductor Compatibility	ACSR-Merlin-336.4-18/1;ACSR-Linnet-336.4-26/7;ACSR-Oriole-336.4-30/7;ACSR-Chickadee-397.5-18/1;ACSR-Brant-397.5-24/7;ACSR-Ibis-397.5-26/7;ACSR-Lark-397.5-30/7;ACSR-Pelican-477-18/1;ACSR-Flicker-477-24/7;ACSR-Hawk-477-26/7;ACSR-Hen-477-30/7;ACSR-Osprey-556.5-18/1;ACSR-Brahma-203.2-16/19;AAC-Canna-397.5-19;AAC-Cosmos-477-19;AAC-Syringa-477-37;AAC-Zinnia-500-19;AAC-Hyacinth-500-37;AAC-Dahlia-556.5-19;AAC-Mistletoe-556.5-37;AAC-Meadowsweet-600-37
Conductor Diameter - Maximum	0.893 in
Conductor Diameter - Minimum	0.681 in
Conductor Diameter Range	0.681 - 0.893
Conductor Spacing	8 in
Conductor Type	<ul style="list-style-type: none"><li>• AAC</li><li>• ACSR</li></ul>

### Product Assets

[Catalogs - Substation Connectors \(SA\)](#)

[Sales Drawings - C-11255 \(APCSF Product Family\)](#)

[Video - Hubbell Power Systems 3D Portal to help with developing 3D models of substation connector products \(VI05050E0619\)](#)

[Video - Hubbell Power Systems Quick Ship \(VI05124E1018\)](#)