

Cable Spacer, Bronze

By ANDERSON
Catalog # [BPCS100212](#)



Bronze alloy, parallel cable spacer for maintaining cable clearance and preventing loose cable damage. Recommended for slack spans only.

*Representative Image

Features

- Bronze Cable Spacer, 2.5 in Spacing, range 0.998 - 1.152 inches (750-1000 MCM)
- Recommended for slack spans only
- Material: Casting - bronze alloy, Hardware - Stainless Steel

General

Catalog Number	BPCS100212
EU RoHS Indicator	No
Material	Bronze
Material - Clamping Hardware	Stainless Steel
Number of Ground Braid Lug	0
Holes	
Type	Cable Spacer
UPC	096359292159

Dimensions

Base Hole Spacing	0 in
Diameter - Base Holes	0 in
Diameter - Bolt	0 in
Diameter - Inside	0 in
Length - Coupling	0 in
Length Before Compression	0 in
Weight	2.94 lb

Electrical Ratings

Maximum Current Rating Amps 0
Continuous

Conductor Related

Conductor Diameter - Maximum	1.152 in
Conductor Diameter - Minimum	0.998 in
Conductor Diameter Range	0.998 - 1.152
Conductor Spacing	2.5 in
Conductor Type	Copper

Certifications And Compliance

Buy American Compliant Contact Manufacturer

Product Assets

- [Catalogs - Substation Connectors \(SA\)](#)
- [Sales Drawings - C-12901 \(BPCS Product Family\)](#)
- [Specifications - BPCS100212](#)
- [Video - Hubbell Power Systems 3D Portal to help with developing 3D models of substation connector products](#)
- [Video - Hubbell Power Systems Quick Ship](#)