

# HUBBELL

## Power Systems

### Anchor Shackle - 30k lb

By ANDERSON  
Catalog # [AS25BNK](#)

Anchor Shackles are used to attach hardware to the tower pad. Back to back anchor shackles are commonly used at the tower attachment point to orient the plane of the tower plate and the balance of the insulator hardware.



#### Features

- UTS 30,000 lbs
- 0.875" opening
- 0.625" bolt
- BNK suffix are furnished with Bolt, Nut and Cotter Key
- Material: Body is Galv. Steel, Hardware is Galv. Steel & Cotter Pin is Stainless Steel

#### General

Material	Steel
Material - Pin (Clevis)	Galvanized Steel
Material - Pin (Cotter)	Stainless Steel
Number of Bolt Holes	0
Series	AS Series
Strength Rating - Ultimate	30000 lb
Strength Rating - Ultimate	0 lb
Body	
UPC	096359285021

#### Dimensions

Assembly Rating (Ultimate)	0 lb
Clevis Opening	0.875 in
Diameter - Bolt	0 in
Diameter - Pin	0 in
Dimensions	3.01 in x 1.76 in x 1.38 in
Height	1.38 in
Insulator Throat Diameter - Maximum	0 in
Insulator Throat Diameter - Minimum	0 in
Insulator Throat Diameter Range	0 - 0
Length	3.01 in
Length - Coupling	2.375 in
Length - Pin	0 in
Maximum Adjustment	0 in
Ring Height	0 in
Weight	1.08 lb
Width	1.76 in

#### Conductor Related

Conductor Diameter - Maximum	0 in
Conductor Spacing	0 in

#### Logistics

Pallet Quantity	2400
-----------------	------

#### Product Assets

[Catalogs - Transmission Connectors Catalog - Full](#)  
[Sales Drawings - AS25BNK Drawing](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
AN-AS25BNK-SPEC-EN | REV 6/2024