

Tee, Aluminum Bolted

By ANDERSON
Catalog # [ATCC1613](#)



Aluminum alloy, cable to cable tee for connecting aluminum-aluminum or aluminum-copper conductor combinations. Clamping bolts have hex stops for one wrench installation. Contact sealant is recommended.

Features

- Tee, Aluminum Bolted, Cable to Cable
- MAIN: 1272-1590 MCM ACSR (1.382-1.632 in. dia.), TAP: 715.5-1113 MCM ACSR (1.081-1.293 in. dia.)
- Castings are 356-T6 Aluminum Alloy
- Clamping Hardware is Aluminum Alloy
- Clamping bolts have hex-stops for one-wrench installation
- Cable contact inhibitor is recommended

General

Catalog Number	ATCC1613
EU RoHS Indicator	No
Material	Aluminum
Material - Clamping Hardware	Aluminum Alloy
Number of Ground Braid Lug	0
Holes	
Type	Tee, Bolted
UPC	096359348337

Dimensions

Base Hole Spacing	0 in
Diameter - Base Holes	0 in
Diameter - Bolt	0 in
Diameter - Inside	0 in
Length - Coupling	0 in
Length Before Compression	0 in
Weight	3.038 lb

Electrical Ratings

Maximum Current Rating Amps	0
Continuous	

Conductor Related

Conductor Compatibility	ACSR-Redwing-715.5-30/19;ACSR-Cuckoo-795-24/7;ACSR-Drake-795-26/7;ACSR-Condor-795-54/7;ACSR-Mallard-795-30/19;ACSR-Ruddy-900-45/7;ACSR-Canary-900-54/7;ACSR-Rail-954-45/7;ACSR-Cardinal-954-
-------------------------	--

	54/7;ACSR-Ortolan-1033.5-45/7;ACSR-Curlew-1033.5-54/7;ACSR-Bluejay-1113-45/7;ACSR-Finch-1113-54/19;ACSR-Pheasant-1272-54/19;ACSR-Dipper-1351.5-45/7;ACSR-Martin-1351.5-54/19;ACSR-Bobolink-1431-45/7;ACSR-Plover-1431-54/19;ACSR-Nuthatch-1510.5-45/7;ACSR-Parrot-1510.5-54/19;ACSR-Lapwing-1590-45/7;ACSR-Falcon-1590-54/19;ACSR-Chukar-1780-84/19;AAC-Cockscomb-900-37;AAC-Snapdragon-900-61;AAC-Magnolia-954-37;AAC-Goldenrod-954-61;AAC-Camellia-1000-61;AAC-Bluebell-1033.5-37;AAC-Larkspur-1033.5-61;AAC-Marigold-1113-61;AAC-Hawthorn-1192.5-61;AAC-Gladiolus-1510.5-61;AAC-Coreopsis-1590-61;AAC-Cowslip-2000-91
Conductor Diameter (Main) - Maximum	1.632 in
Conductor Diameter (Main) - Minimum	1.382 in
Conductor Diameter (Main) Range	1.382 - 1.632
Conductor Diameter (Tap) - Maximum	1.108 in
Conductor Diameter (Tap) - Minimum	0.87 in
Conductor Type	• AAC • ACSR

Certifications And Compliance

Buy America(n) Qualified	BABA Compliant (All status valid till December 2024)
--------------------------	--

Product Assets

[Catalogs - Substation Connectors \(SA\)](#)
[Sales Drawings - C-1279 \(ATCC Product Family\)](#)
[Specifications - ATCC1613](#)

[Video - Hubbell Power Systems 3D Portal to help with developing 3D models of substation connector products](#)
[Video - Hubbell Power Systems Quick Ship](#)



A Hubbell brand

©2025 Hubbell Incorporated. All rights reserved
AN-ATCC1613-SPEC-EN | REV 3/2025