

Tee, Aluminum Bolted

By ANDERSON
Catalog # [ATCC169](#)

Tee, Aluminum Bolted, Cable to Cable, MAIN: 1272-1590 MCM ACSR (1.382-1.632 in. dia.), TAP: 336.4-477 MCM ACSR (0.681-0.893 inch dia.)



*Representative Image

Features

- Castings are 356-T6 Aluminum Alloy
- Clamping Hardware is Aluminum Alloy
- Clamping bolts have hex-stops for one-wrench installation
- Cable contact inhibitor is recommended

General

EU RoHS Indicator	No
Material	Aluminum
Material - Clamping Hardware	Aluminum Alloy
Type	Tee, Bolted
UPC	096359286929

Dimensions

Weight	2.842 lb
--------	----------

Conductor Related

Conductor Compatibility	ACSR-Merlin-336.4-18/1;ACSR-Linnet-336.4-26/7;ACSR-Oriole-336.4-30/7;ACSR-Chickadee-397.5-18/1;ACSR-Brant-397.5-24/7;ACSR-Ibis-397.5-26/7;ACSR-Lark-397.5-30/7;ACSR-Pelican-477-18/1;ACSR-Flicker-477-24/7;ACSR-Hawk-477-26/7;ACSR-Hen-477-30/7;ACSR-Osprey-556.5-18/1;ACSR-Pheasant-1272-54/19;ACSR-Dipper-1351.5-45/7;ACSR-Martin-1351.5-54/19;ACSR-Bobolink-1431-45/7;ACSR-Plover-1431-54/19;ACSR-Nuthatch-1510.5-45/7;ACSR-Parrot-1510.5-45/7;ACSR-Lapwing-1590-45/7;ACSR-Falcon-1590-54/19;ACSR-Chukar-1780-84/19;ACSR-Brahma-203.2-16/19;AAC-Canna-397.5-19;AAC-Cosmos-477-19;AAC-Syringa-477-37;AAC-Zinnia-500-19;AAC-Hyacinth-500-37;AAC-Dahlia-556.5-19;AAC-Mistletoe-556.5-37;AAC-Meadowsweet-600-37;AAC-Gladiolus-1510.5-61;AAC-Coreopsis-1590-61;AAC-Cowslip-2000-91
Conductor Diameter (Main) - Maximum	1.632 in
Conductor Diameter (Main) - Minimum	1.382 in
Conductor Diameter (Main) Range	1.382 - 1.632
Conductor Diameter (Tap) - Maximum	0.893 in
Conductor Diameter (Tap) - Minimum	0.681 in
Conductor Type	<ul style="list-style-type: none"> • AAC • ACSR

Product Assets

[Catalogs - Substation Connectors \(SA\)](#)
[Sales Drawings - C-1279 \(ATCC Product Family\)](#)



A proud member of the Hubbell Family.