

# HUBBELL Power Systems

## Clevis-Clevis Fitting

By ANDERSON  
Catalog # [CCC25](#)

Clevis Clevises are used to attach clevis tongue insulators to various associated hardware within an insulator string. Material: body - galvanized ductile iron, clevis pin - galvanized steel, cotter pin - stainless steel.



### Features

"BNK" suffix if added replaces clevis pin & cotter pin with bolt, nut & cotter pin

### General

Coupling Orientation	Straight
EU RoHS Indicator	No
Material	Ductile Iron
Material - Pin (Clevis)	Galvanized Steel
Material - Pin (Cotter)	Stainless Steel
Number of Bolt Holes	0
Series	CCC Series
Strength Rating - Ultimate	25000 lb
Strength Rating - Ultimate Body	0 lb
UPC	096359297079

### Dimensions

Assembly Rating (Ultimate)	0 lb
Diameter - Bolt	0 in
Diameter - Pin	0 in
Height	2.689 in
Insulator Throat Diameter - Maximum	0 in
Insulator Throat Diameter - Minimum	0 in
Insulator Throat Diameter Range	0 - 0
Length - Coupling	3 in
Length - Pin	0 in
Maximum Adjustment	0 in
Ring Height	0 in
Weight	2.45 lb
Width	4.75 in

### Conductor Related

Conductor Diameter - Maximum	0 in
Conductor Spacing	0 in

### Product Assets

[Catalogs - Transmission Connectors Catalog - Full Sales Drawings - CCC25](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
AN-CCC25-SPEC-EN | REV 6/2024