

Tee, Aluminum Bolted

By ANDERSON
Catalog # [ATCC99](#)

Tee, Aluminum Bolted, Cable to Cable, MAIN: 336.4-477 MCM ACSR (0.681-0.893 inch dia.), TAP: 336.4-477 MCM ACSR (0.681-0.893 inch dia.)



*Representative Image

Features

- Castings are 356-T6 Aluminum Alloy
- Clamping Hardware is Aluminum Alloy
- Clamping bolts have hex-stops for one-wrench installation
- Cable contact inhibitor is recommended

General

Material	Aluminum
Material - Clamping Hardware	Aluminum Alloy
Type	Tee, Bolted
UPC	096359287032

Dimensions

Length	3.25 in
Weight	1.96 lb
Width	6.063 in

Conductor Related

Conductor Compatibility	ACSR-Merlin-336.4-18/1;ACSR-Linnet-336.4-26/7;ACSR-Oriole-336.4-30/7;ACSR-Chickadee-397.5-18/1;ACSR-Brant-397.5-24/7;ACSR-Ibis-397.5-26/7;ACSR-Lark-397.5-30/7;ACSR-Pelican-477-18/1;ACSR-Flicker-477-24/7;ACSR-Hawk-477-26/7;ACSR-Hen-477-30/7;ACSR-Osprey-556.5-18/1;ACSR-Brahma-203.2-16/19;AAC-Canna-397.5-19;AAC-Cosmos-477-19;AAC-Syringa-477-37;AAC-Zinnia-500-19;AAC-Hyacinth-500-37;AAC-Dahlia-556.5-19;AAC-Mistletoe-556.5-37;AAC-Meadowsweet-600-37
Conductor Diameter (Main) - Maximum	0.893 in
Conductor Diameter (Main) - Minimum	0.681 in
Conductor Diameter (Main) Range	0.681 - 0.893
Conductor Diameter (Tap) - Maximum	0.893 in
Conductor Diameter (Tap) - Minimum	0.681 in
Conductor Type	<ul style="list-style-type: none"> • AAC • ACSR

Logistics

Pallet Quantity	504
-----------------	-----

Product Assets

[Catalogs - Substation Connectors \(SA\)](#)
[Sales Drawings - C-1279](#)

[Video - Hubbell Power Systems 3D Portal to help with developing 3D models of substation connector products \(VI05050E0619\)](#)

[Video - Hubbell Power Systems Quick Ship \(VI05124E1018\)](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
AN-ATCC99-SPEC-EN | REV 1/2024