

Tee, Aluminum Bolted

By ANDERSON
Catalog # [ATT2C4011](#)

"Tees Bolted, Connecting Tubing Main to Cable Tap, Tubing Main-IPS/EHIPS-1-1/2", Cable Tap- AAC- 250-400 MCM, ACSR- 4/0-336.4 MCM, Dia.- 0.563"-0.744", Material: Castings- Aluminum Alloy, Hardware- Aluminum Alloy"



*Representative Image

Features

- "Tee for Connecting Aluminum-Aluminum or Aluminum-Copper Conductor Combinations "

General

EU RoHS Indicator	No
Material	Aluminum
Material - Clamping Hardware	Aluminum Alloy
Type	Bolted Tees
UPC	096359288084

Dimensions

Weight	6.566 lb
--------	----------

Conductor Related

Conductor Compatibility	ACSR-Hen-477-30/7;ACSR-Osprey-556.5-18/1;ACSR-Parakeet-556.5-24/7;ACSR-Dove-556.5-26/7;ACSR-Eagle-556.5-30/7;ACSR-Peacock-605-24/7;ACSR-Squab-605-26/7;ACSR-Teal-605-30/19;ACSR-Kingbird-636-18/1;ACSR-Swift-636-36/1;ACSR-Rook-636-24/7;ACSR-Grosbeak-636-26/7;ACSR-Egret-636-30/19;ACSR-Flamingo-666.6-24/7;ACSR-Gannet-666.6-26/7;ACSR-Stilt-715.5-24/7;ACSR-Starling-715.5-26/7;ACSR-Redwing-715.5-30/19;ACSR-Coot-795-36/1;ACSR-Cuckoo-795-24/7;ACSR-Drake-795-26/7;ACSR-Tern-795-45/7;ACSR-Condor-795-54/7;AAC-Meadowsweet-600-37;AAC-Orchid-636-37;AAC-Flag-700-61;AAC-Violet-715.5-37;AAC-Nasturtium-715.5-61;AAC-Cattail-750-61;AAC-Arbutus-795-37;AAC-Lilac-795-61;AAC-Cockscomb-900-37;AAC-Snapdragon-900-61
Conductor Diameter (Tap) - Maximum	1.108 in
Conductor Diameter (Tap) - Minimum	0.87 in
Conductor Type	Aluminum Bus

Product Assets

[Catalogs - Substation Connectors \(SA\)](#)

[Sales Drawings - C-1753 \(ATT2 Product Family\)](#)

[Video - Hubbell Power Systems 3D Portal to help with developing 3D models of substation connector products \(VI05050E0619\)](#)

[Video - Hubbell Power Systems Quick Ship \(VI05124E1018\)](#)

