

HUBBELL

Power Systems

Clevis-Clevis Fitting

By ANDERSON

Catalog # [CCC80BNK](#)

Clevis Clevises are used to attach clevis tongue insulators to various associated hardware within an insulator string. Material: body - galvanized ductile iron, clevis pin - galvanized steel, cotter pin - stainless steel.



Features

"BNK" suffix if added replaces clevis pin & cotter pin with bolt, nut & cotter pin

General

Coupling Orientation	Straight
EU RoHS Indicator	No
Material	Ductile Iron
Material - Pin (Clevis)	Galvanized Steel
Material - Pin (Cotter)	Stainless Steel
Number of Bolt Holes	0
Series	CCC Series
Strength Rating - Ultimate	80000 lb
Strength Rating - Ultimate	0 lb
Body	
UPC	096359297185

Dimensions

Assembly Rating (Ultimate)	0 lb
Diameter - Bolt	0 in
Diameter - Pin	0 in
Insulator Throat Diameter - Maximum	0 in
Insulator Throat Diameter - Minimum	0 in
Insulator Throat Diameter Range	0 - 0
Length - Coupling	5.125 in
Length - Pin	0 in
Maximum Adjustment	0 in
Ring Height	0 in
Weight	5.88 lb

Conductor Related

Conductor Diameter - Maximum	0 in
Conductor Spacing	0 in

Logistics

Pallet Quantity 162

Product Assets

[Catalogs - Transmission Connectors Catalog - Full](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
AN-CCC80BNK-SPEC-EN | REV 6/2024