

Ball Clevis - 30k lb

By ANDERSON
Catalog # [BC30](#)



Ball clevises are used to attach ball and socket insulators to other associated tower hardware.

Features

- Ball Clevis: 0.938" Opening, 0.625" Pin
- UTS 30,000 lb
- Material: Body is Galv. Steel, Hardware is Galv. Steel & Cotter Pin is Stainless Steel
- For use with class 52-3 and 52-5 insulators per ANSI Spec. C-29.2.71

General

Catalog Number	BC30
Connector Type	Deadend
Fitting Type	52-3/52-5
Item Type	4D
Material	Copper Alloy
Material - Body	Galvanized Steel
Material - Pin (Clevis)	Galvanized Steel
Material - Pin (Cotter)	Stainless Steel
Number of Bolt Holes	0
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	N
Series	BC Series
Strength Rating - Ultimate	30000 lb
Strength Rating - Ultimate	0 lb
Body	
UPC	096359291169
UPC 14 Digit GTIN	007818108910011

Dimensions

Assembly Rating (Ultimate)	0 lb
Clevis Opening	0.63 in
Diameter - Bolt	0 in
Diameter - Clevis Pin	0.63 in
Diameter - Pin	0 in
Dimension - B Length fraction	1-7/8 in
Dimension - B Length inch	1.88 in
Dimension - Height mm	0 mm
Dimension - L Length Overall mm	0 mm
Dimension - Pad Width inch	1.25 in

Dimension - Pin Diameter fraction	1/2 in
Dimension - Pin Diameter inch	0.50 in
Dimension - Width mm	0 mm
Dimensions	1.56 in x 3.03 in x 0.63 in
Height	0.63 in
Insulator Throat Diameter - Maximum	0 in
Insulator Throat Diameter - Minimum	0 in
Insulator Throat Diameter Range	0 - 0
Length	1.56 in
Length - Coupling	2.88 in
Length - Pin	0 in
Maximum Adjustment	0 in
Ring Height	0 in
Weight	1 lb
Width	3.03 in

Conductor Related

Conductor - Copper Str Size	4/0 AWG;250 kcmil;300 kcmil
Conductor - Copper Str Size Range	4/0 AWG-300 kcmil
Conductor Diameter - Maximum	0 in
Conductor Spacing	0 in

Certifications And Compliance

Certification - UL Recognized	N
Certification - cULus	N

Logistics

Pallet Quantity	1800
-----------------	------

Product Assets

[Catalogs - Transmission Connectors Catalog - Full](#)
[Sales Drawings - BC30 Drawing](#)
[Specifications - BC30](#)