

Terminal, Aluminum Compression

By ANDERSON
Catalog # [CCL1382D](#)

Aluminum cast, compression terminal for connecting aluminum cable to flat pad. Connector barrel is filled with rubber compatible sealant and enclosed in clear plastic bag. Contact sealant is recommended on the pads. Pad holes have NEMA spacing. Pads have contact surface on both sides. Short barrel requires less space and allows faster installation. For use with VERSA CRIMP® tooling through CCLS1300 (Die Ref. 1.844) and conventional compression tooling. Refer to Chart C-13282 on page A-34 for tool and die information. Material: casting - 99 aluminum alloy.

Features

"90° pad orientation available, 45° pad orientation available"

General

Catalog Number	CCL1382D
EU RoHS Indicator	No
Material	Aluminum
Number of Bolt Holes	4
Number of Ground Braid Lug Holes	0
Number of Pad Holes	4
Type	Terminal, Cable to Flat
UPC	096359297314

Dimensions

Angle - Pad	180 °
Base Hole Spacing	0 in
Diameter - Base Holes	0 in
Diameter - Bolt	0 in
Diameter - Inside	0 in
Length - Coupling	0 in
Length Before Compression	0 in
Weight	2.744 lb
Width - Pad	4 in

Electrical Ratings



*Representative Image

Maximum Current Rating Amps 0
Continuous

Conductor Related

Conductor Compatibility	ACSR-Bittern-1272-45/7;ACSR-Pheasant-1272-54/19;AAC-Carnation-1431-61
Conductor Diameter - Maximum	1.382 in
Conductor Diameter - Minimum	1.345 in
Conductor Diameter Range	1.345 - 1.382
Conductor Type	<ul style="list-style-type: none">• AAC• ACSR

Certifications And Compliance

Buy American Compliant Contact Manufacturer

Logistics

Pallet Quantity 432

Product Assets

- [Catalogs - Substation Connectors \(SA\)](#)
- [Sales Drawings - C-1974 \(CCL Product Family\)](#)
- [Specifications - CCL1382D](#)
- [Video - Hubbell Power Systems 3D Portal to help with developing 3D models of substation connector products](#)
- [Video - Hubbell Power Systems Quick Ship](#)