

**Cable Spacer, Bronze**

By ANDERSON  
Catalog # [BPCS08012](#)



Bronze alloy, parallel cable spacer for maintaining cable clearance and preventing loose cable damage. Recommended for slack spans only.

**Features**

- Bronze Cable Spacer, 12 in Spacing, Copper cable range 0.811 - 1.031 inches (500-800 MCM)
- Recommended for slack spans only
- Material: Casting - bronze alloy, Hardware - Stainless Steel

**General**

Catalog Number	BPCS08012
EU RoHS Indicator	No
Material	Bronze
Material - Clamping Hardware	Stainless Steel
Number of Ground Braid Lug	0
Holes	
Type	Cable Spacer
UPC	096359292104

**Dimensions**

Base Hole Spacing	0 in
Diameter - Base Holes	0 in
Diameter - Bolt	0 in
Diameter - Inside	0 in
Length - Coupling	0 in
Length Before Compression	0 in
Weight	5.88 lb

**Electrical Ratings**

Maximum Current Rating Amps 0  
Continuous

**Conductor Related**

Conductor Diameter - Maximum	1.031 in
Conductor Diameter - Minimum	0.811 in
Conductor Diameter Range	0.811 - 1.031
Conductor Spacing	12 in
Conductor Type	Copper

**Certifications And Compliance**

Buy America(n) Qualified      Contact Manufacturer

**Product Assets**

- [Catalogs - Substation Connectors \(SA\)](#)
- [Sales Drawings - C-12901 \(BPCS Product Family\)](#)
- [Specifications - BPCS08012](#)
- [Video - Hubbell Power Systems 3D Portal to help with developing 3D models of substation connector products](#)
- [Video - Hubbell Power Systems Quick Ship](#)