

Terminal, Aluminum Compression

By ANDERSON
Catalog # [CCLS953B2](#)

Terminal, Aluminum Compression, Cable to Flat, Short Barrel,
Cable range: 0.879-0.953 in. Pad: 2 hole, 2 in. wide (NEMA B2)



Features

- Cast Aluminum
- Connector barrel prefilled with inhibitor
- Inhibitor is recommended for pad connection
- Pad is in-line with compression barrel

General

EU RoHS Indicator	No
Material	Aluminum
Number of Bolt Holes	2
Number of Pad Holes	2
Type	Terminal, Cable to Flat
UPC	096359298199

Dimensions

Angle - Pad	180 °
Weight	0.784 lb
Width - Pad	2 in

Conductor Related

Conductor Compatibility	ACSR-Hen-477-30/7;ACSR-Osprey-556.5-18/1;ACSR-Parakeet-556.5-24/7;ACSR-Dove-556.5-26/7;ACSR-Eagle-556.5-30/7;ACSR-Peacock-605-24/7;ACSR-Kingbird-636-18/1;ACSR-Swift-636-36/1;AAC-Meadowsweet-600-37;AAC-Orchid-636-37
Conductor Diameter - Maximum	0.953 in
Conductor Diameter - Minimum	0.879 in
Conductor Diameter Range	0.879 - 0.953
Conductor Type	<ul style="list-style-type: none">• AAC• ACSR

Product Assets

- [Catalogs - Substation Connectors \(SA\)](#)
- [Sales Drawings - CC-14256 \(CCLS B and B2 Product Family\)](#)
- [Video - Hubbell Power Systems 3D Portal to help with developing 3D models of substation connector products \(VI05050E0619\)](#)
- [Video - Hubbell Power Systems Quick Ship \(VI05124E1018\)](#)