

# HUBBELL


## Power Systems

### Cable Spacer, Bronze

By ANDERSON

Catalog # [BPCS0804](#)

Bronze alloy, parallel cable spacer for maintaining cable clearance and preventing loose cable damage. Recommended for slack spans only.



\*Representative Image

#### Features

- Bronze Cable Spacer, 4 in Spacing, Copper cable range 0.811 - 1.031 inches (500-800 MCM)
- Recommended for slack spans only
- Material: Casting - bronze alloy, Hardware - Stainless Steel

#### General

EU RoHS Indicator	No
Material	Bronze
Material - Clamping Hardware	Stainless Steel
Number of Ground Braid Lug Holes	0
Type	Cable Spacer
UPC	096359292111

#### Dimensions

Base Hole Spacing	0 in
Diameter - Base Holes	0 in
Diameter - Bolt	0 in
Diameter - Inside	0 in
Length - Coupling	0 in
Length Before Compression	0 in
Weight	4.508 lb

#### Electrical Ratings

Maximum Current Rating Amps 0  
Continuous

#### Conductor Related

Conductor Diameter - Maximum	1.031 in
Conductor Diameter - Minimum	0.811 in
Conductor Diameter Range	0.811 - 1.031
Conductor Spacing	4 in
Conductor Type	Copper

#### Logistics

Pallet Quantity 420

#### Product Assets

[Catalogs - Substation Connectors \(SA\)](#)

[Sales Drawings - C-12901 \(BPCS Product Family\)](#)

[Video - Hubbell Power Systems 3D Portal to help with](#)

[developing 3D models of substation connector products](#)

[Video - Hubbell Power Systems Quick Ship](#)



**A Hubbell brand**

©2024 Hubbell Incorporated. All rights reserved  
AN-BPCS0804-SPEC-EN | REV 6/2024