

Clevis Eye, Rotated 90-deg

By ANDERSON
Catalog # [CE02504](#)

Clevis Eye, Rotated, Ductile Iron, Clevis: 0.875" Opening,
0.625" Pin, Eye: 0.500" width w/ 0.688" Hole, UTS 20,000 lb



*Representative Image

Features

- "BNK" suffix if added replaces clevis pin & cotter pin with bolt, nut & cotter pin

General

| | |
|----------------------------|------------------|
| Material | Ductile Iron |
| Material - Pin (Clevis) | Galvanized Steel |
| Material - Pin (Cotter) | Stainless Steel |
| Series | CE Series |
| Strength Rating - Ultimate | 20000 lb |
| UPC | 096359298304 |

Dimensions

| | |
|---------------------------------|----------|
| Diameter - Eye Hole | 0.688 in |
| Insulator Throat Diameter Range | 0 - 0 |
| Length - Coupling | 2.625 in |
| Weight | 1.372 lb |
| Width - Eye | 0.5 in |

Logistics

| | |
|-----------------|------|
| Pallet Quantity | 1440 |
|-----------------|------|

Product Assets

[Catalogs - Transmission Connectors Catalog - Full \(CA05063E\)](#)
[Sales Drawings - C-11403](#)