

## Cable Spacer, Bronze

By ANDERSON  
Catalog # [BPCS1006](#)

Bronze Cable Spacer, 6 in Spacing, range 0.998 - 1.152 inches  
(750-1000 MCM)



\*Representative Image

### Features

- Recommended for slack spans only

### General

EU RoHS Indicator	No
Material	Bronze
Material - Clamping Hardware	Stainless Steel
Number of Ground Braid Lug Holes	0
Type	Cable Spacer
UPC	096359292173

### Dimensions

Base Hole Spacing	0 in
Diameter - Base Holes	0 in
Diameter - Bolt	0 in
Diameter - Inside	0 in
Length - Coupling	0 in
Length Before Compression	0 in
Weight	6.468 lb

### Electrical Ratings

Maximum Current Rating Amps Continuous	0
---	---

### Conductor Related

Conductor Diameter - Maximum	1.152 in
Conductor Diameter - Minimum	0.998 in
Conductor Diameter Range	0.998 - 1.152
Conductor Spacing	6 in
Conductor Type	Copper

### Logistics

Pallet Quantity	216
-----------------	-----

### Product Assets

[Catalogs - Substation Connectors \(SA\)](#)

[Sales Drawings - C-12901 \(BPCS Product Family\)](#)

[Video - Hubbell Power Systems 3D Portal to help with developing 3D models of substation connector products \(VI05050E0619\)](#)

[Video - Hubbell Power Systems Quick Ship \(VI05124E1018\)](#)