

Terminal, Aluminum Compression

By ANDERSON
Catalog # [CCLS1424D](#)

Terminal, Aluminum Compression, Cable to Flat, Short Barrel,
Cable range: 1.345-1.424 in. Pad: 4 hole, 4 in. wide (NEMA D)



*Representative Image

Features

- Cast Aluminum
- Connector barrel prefilled with inhibitor
- Inhibitor is recommended for pad connection
- Pad is in-line with compression barrel

General

EU RoHS Indicator	No
Material	Aluminum
Number of Bolt Holes	4
Number of Pad Holes	4
Type	Terminal, Cable to Flat
UPC	096359297772

Dimensions

Angle - Pad	180 °
Weight	1.960 lb
Width - Pad	4 in

Conductor Related

Conductor Compatibility	ACSR-Bittern-1272-45/7;ACSR-Pheasant-1272-54/19;ACSR-Dipper-1351.5-45/7;ACSR-Martin-1351.5-54/19;AAC-Carnation-1431-61;AAC-Gladiolus-1510.5-61
Conductor Diameter - Maximum	1.424 in
Conductor Diameter - Minimum	1.345 in
Conductor Diameter Range	1.345 - 1.424
Conductor Type	<ul style="list-style-type: none">• AAC• ACSR

Product Assets

- [Catalogs - Substation Connectors \(SA\)](#)
- [Sales Drawings - CC-13147 \(CCLS C and D Product Family\)](#)
- [Video - Hubbell Power Systems 3D Portal to help with developing 3D models of substation connector products \(VI05050E0619\)](#)
- [Video - Hubbell Power Systems Quick Ship \(VI05124E1018\)](#)