

HUBBELL

Power Systems

Stud Connector, Bronze

By ANDERSON

Catalog # [D2S1110012](#)

Bronze alloy stud connector for connecting two copper cables or tubes to equipment stud. A wide range of cable or a limited range of tubing may accommodate straight or 90 degree connections. Clamping bolts have hex-stops for one-wrench installation.



Features

- "To specify 90 degree connector, insert "90" into catalog number. Example: DSC0602590163
- All sizes furnished with reversible cable caps"

General

EU RoHS Indicator	No
Material	Bronze
Material - Clamping Hardware	Stainless & Galvanized Steel
Number of Ground Braid Lug Holes	0
Number of Stud Threads	12
Type	Stud to Tube or Cable
UPC	096359299592

Dimensions

Base Hole Spacing	0 in
Diameter - Base Holes	0 in
Diameter - Bolt	0 in
Diameter - Inside	0 in
Diameter - Stud	1.125 in
Length - Coupling	0 in
Length Before Compression	0 in
Weight	6.958 lb

Electrical Ratings

Maximum Current Rating Amps 0
Continuous

Conductor Related

Conductor Diameter - Maximum	1.152 in
Conductor Diameter - Minimum	0.258 in
Conductor Diameter Range	0.258 - 1.152
Conductor Type	Copper

Product Assets

[Catalogs - Substation Connectors \(SA\)](#)
[Sales Drawings - CC-1817 \(D2S Product Family\)](#)
[Video - Hubbell Power Systems 3D Portal to help with developing 3D models of substation connector products](#)
[Video - Hubbell Power Systems Quick Ship](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
AN-D2S1110012-SPEC-EN | REV 6/2024