

HUBBELL Power Systems

Clevis Eye, Rotated 90-deg

By ANDERSON

Catalog # [CE02506](#)

Type CE Clevis Eyes are used to connect quadrant type deadends to clevis tongue insulators or yoke plates. The eye type CE is 90° from type CA. Material: body - galvanized ductile iron, clevis pin - galvanized steel, cotter pin - stainless steel.



*Representative Image

Features

"BNK" suffix if added replaces clevis pin & cotter pin with bolt, nut & cotter pin

General

EU RoHS Indicator	No
Material	Ductile Iron
Material - Pin (Clevis)	Galvanized Steel
Material - Pin (Cotter)	Stainless Steel
Number of Bolt Holes	0
Series	CE Series
Strength Rating - Ultimate	25000 lb
Strength Rating - Ultimate	0 lb
Body	
UPC	096359298311

Dimensions

Assembly Rating (Ultimate)	0 lb
Diameter - Bolt	0 in
Diameter - Eye Hole	0.688 in
Diameter - Pin	0 in
Insulator Throat Diameter - Maximum	0 in
Insulator Throat Diameter - Minimum	0 in
Insulator Throat Diameter Range	0 - 0
Length - Coupling	2.625 in
Length - Pin	0 in
Maximum Adjustment	0 in
Ring Height	0 in
Weight	1.666 lb
Width - Eye	0.75 in

Conductor Related

Conductor Diameter - Maximum	0 in
Conductor Spacing	0 in

Logistics

Pallet Quantity 1440

Product Assets

[Catalogs - Transmission Connectors Catalog - Full](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
AN-CE02506-SPEC-EN | REV 6/2024